



ZEISS AT LARA 829MP preloaded
Technical Specifications



ZEISS AT LARA 829MP preloaded

AT LARA 829MP preloaded



Optic Design	Diffractive, aspheric. Depth of Focus Extensions: 0.95 D and 1.9 D
Material	Hydrophilic acrylate (25 % water content) with hydrophobic surface properties
Optic Diameter	6.0 mm
Total Diameter	11.0 mm
Haptic Angulation	0°
Lens Design	Single-piece MICS
Incision Size	1.8 mm
Company Labeled A-Constant	118.5
Diopter Range	-10.0 to +32.0 D, 0.5 D increments
ACD	5.20
Implantation in	Capsular Bag
Injector/Cartridge Set	BLUEMIXS® 180
Indications	Senile cataracts and other forms of cataract. Visual correction of aphakia in patients with and without presbyopia.

CE 0297 AT LARA

CE 0459 BLUEMIXS 180 injector



Carl Zeiss Meditec AG
Goeschitzer Str. 51–52
07745 Jena
Germany
www.zeiss.com/lara
www.zeiss.com/med/contacts



Carl Zeiss Meditec SAS
27 Avenue Paul Langevin
17180 Périgny
France

EN_32_022_00581

AT LARA and BLUEMIXS are registered trademarks of Carl Zeiss Meditec.

The contents of the brochure may differ from the current status of approval of the product in your country. Please contact our regional representative for more information. Subject to change in design and scope of delivery and as a result of ongoing technical development. Printed on elemental chlorine-free bleached paper.

© 2017 by Carl Zeiss Meditec AG. All copyrights reserved.